

# Accura® Fidelity™

Manufacture high yield investment casting patterns with ultra-low viscosity, antimony-free stereolithography (SLA) resin.

**Casting Class**  
Stereolithography (SLA)

## INVESTMENT CASTING PATTERNS STABILITY AND CLEAN BURNOUT

QuickCast® investment castings patterns printed with Accura Fidelity lead to an increase in casting yields. Designed for a variety of castable metals, this antimony free, low viscosity clean burn resin is perfect for titanium alloy.

Combined with cutting edge software, Accura Fidelity quickly creates large, light weight, and easy to handle casting patterns through our industry leading QuickCast process.

## Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	130 cps
Penetration Depth (Dp)		5.28 mils
Critical Exposure (Ec)		12.8 mJ/cm <sup>2</sup>
Color		Clear / Transparent
Liquid Density	@ 25 °C (77 °F)	1.13 g/cm <sup>3</sup>   0.04 lbs/in <sup>3</sup>

## APPLICATIONS

- Medium to large size patterns without tooling
- One-off investment castings
- Low production runs investment castings
- Any casting materials

## BENEFITS

- Accurate QuickCast patterns
- Clean burnout with ultra-low ash content (<0.010%)
- Patterns dimensional stability
- Fast and effective pattern draining
- Designed to eliminate bubble formation

## FEATURES

- Antimony-free material
- Ultra-low coefficient of thermal expansion
- Excellent humidity/moisture resistance
- Low viscosity material
- Transparent material

# Accura® Fidelity™


Manufacture high yield investment casting patterns with ultra-low viscosity, antimony-free stereolithography (SLA) resin.

Casting Class  
Stereolithography (SLA)

## Post-Cured Material

MECHANICAL PROPERTIES			
MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa   PSI)	ASTM D638	65	18900
Tensile Modulus (MPa   KSI)	ASTM D638	2790	809
Elongation at Break	ASTM D638	5-11%	
Flexural Strength (MPa   PSI)	ASTM D790	124	36000
Flexural Modulus (MPa   KSI)	ASTM D790	2400	696
Notched Izod Impact Strength (J/m   Ft-lbs/in)	ASTM D256	25-39	0.47-0.73
Heat Deflection Temperature @ 0.45 MPa (66 PSI) @ 1.82 MPa (264 PSI)	ASTM D648	63 °C	146 °F
		55 °C	130 °F
Coefficient of Thermal Expansion (CTE) ( $\mu\text{m}/\text{m}\cdot\text{°C}$   $\mu\text{in}/\text{in}\cdot\text{°F}$ )	ASTM E831-93 -40-0°C (-40-32°F) 0-55°C (32-131°F) 55-90°C (131-194°F) 90-140°C (194-284°F)	62	34
		78	43
		124	69
		166	92
Glass Transition (Tg)	DMA, E''	61 °C	141 °F
Hardness, Shore D		84	
Water Absorption at Saturation	ASTM D570-98	0.38%	
Solid Density (g/cm <sup>3</sup>   lbs/in <sup>3</sup> )	@ 25 °C (77 °F)	1.19	0.043
Ash Content	TGA	<0.010%*	
Antimony Content (ICP)	ASTM 6020B	<0.1 ppm	

\* Measured value within TGA device resolution.



[www.3dsystems.com](http://www.3dsystems.com)

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, Accura and QuickCast are registered trademarks, and Fidelity is a trademark of 3D Systems, Inc.